

**End cutter, polished, overall length: 160mm****Order data**

Order number	721100 160
GTIN	4003773040620
Item class	73F

Description**Version:**

Sturdy head with short joint. Cutting edges induction hardened (approx. 64 HRC). Jaws chemically blacked, polished head, plastic coated handles. High cutting capacity due to optimum leverage.

Standard:

DIN ISO 5748

Material:

Chrome-vanadium high-performance steel, forged, multi-stage oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	4.5 mm
overall length	160 mm
Cutting capacity hard wire up to Ø	2.5 mm
Cutting capacity piano wire up to Ø	2 mm
Standard	DIN ISO 5748
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chrome vanadium steel
Surface	chemically blacked

Head	polished
Type of product	Cutting pliers