



X-Cut® compact side cutter, chrome-plated with grips VDE insulated, overall length: 160 mm



Order data

Order number	724310 160
GTIN	4003773075141
Item class	73F

Description

Version:

With slim head with induction hardened cutting edges (approx. 64 HRC). **Box joint** for maximum stability.

Jaws chrome-plated, handles with multi-component covering.

Insulated to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Cutting capacity soft wire up to Ø: 4.8 mm

Cutting capacity hard wire up to Ø: 2.7 mm

Cutting capacity piano wire up to Ø: 2.2 mm

Technical description

overall length	160 mm
Cutting capacity soft wire up to Ø	4.8 mm
Cutting capacity piano wire up to Ø	2.2 mm
Cutting capacity hard wire up to Ø	2.7 mm
Manufacturer's designation	X-Cut
Standard	DIN EN 60900 / VDE 0682-201

Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Special tool steel
Surface	chrome-plated
Type of product	Cutting pliers