



## Heavy-duty side cutter, chrome-plated VDE dip insulated, overall length: 200mm



### Order data

Order number	723535 200
GTIN	4003773018414
Item class	73F

### Description

#### Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws chrome-plated, plastic coated handles, **dip insulated**.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

#### Standard:

**DIN ISO 5749**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

### Technical description

overall length	200 mm
Cutting capacity hard wire up to Ø	3 mm
Cutting capacity soft wire up to Ø	4.2 mm
Cutting capacity piano wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers