

Garant**Heavy-duty side cutter, chrome-plated, with grips, overall length: 180mm****Order data**

Order number	723040 180
GTIN	4045197416995
Item class	71B

Description**Version:**

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	2.2 mm
Cutting capacity soft wire up to Ø	3.8 mm
overall length	180 mm
Cutting capacity hard wire up to Ø	2.7 mm
Standard	DIN ISO 5749
Handle	Multi-component covering with non-slip Haptoprene surface

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers