

Garant**Side cutter chrome-plated, with grips, overall length: 140mm**

Order data

Order number	724840 140
GTIN	4045197417015
Item class	71B

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity hard wire up to Ø	1.8 mm
Cutting capacity soft wire up to Ø	2.8 mm
overall length	140 mm
Standard	DIN ISO 5749
Handle	Multi-component covering with non-slip Haptoprene surface
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated

Data sheet

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers