



Heavy-duty side cutter, chrome-plated VDE insulated, overall length: 160mm



Order data

Order number	723500 160
GTIN	4003773040705
Item class	73F

Description

Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws chrome-plated, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Cutting capacity piano wire up to Ø	2 mm
Cutting capacity soft wire up to Ø	3.4 mm
Cutting capacity hard wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel

Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers