



## Mechanic's end cutter chrome-plated, overall length: 130 mm



### Order data

Order number	721500 130
GTIN	4003773018001
Item class	73F

### Description

#### Version:

Slim shape with induction hardened cutting edges. Inlaid joint. Pliers chrome-plated, plastic coated handles.

#### Application:

Lightweight model for thin wires.

#### Standard:

**DIN ISO 5748**

#### Material:

Chrome-vanadium high-performance steel, forged and multi-stage oil-hardened.

Cutting capacity soft wire up to  $\varnothing$ : 0.4 - 2 mm

Cutting capacity hard wire up to  $\varnothing$ : 1 mm

Cutting capacity piano wire up to  $\varnothing$ : 0.8 mm

### Technical description

Cutting capacity piano wire up to $\varnothing$	0.8 mm
Cutting capacity soft wire up to $\varnothing$	0.4 - 2 mm
overall length	130 mm
Cutting capacity hard wire up to $\varnothing$	1 mm
Standard	DIN ISO 5748
Handle	plastic coated

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chrome vanadium high-performance steel
Surface	chrome-plated
Type of product	Cutting pliers