

Garant**Screwdriver set for slot-head, with 2-component Haptoprene® handle,
Number of screwdrivers: 5****Order data**

Order number	660031 5
GTIN	4045197923219
Item class	61F

Description**Version:**

Versatile, robust screwdriver with taper blade.

Power grip with non-allergenic, easy-grip **Haptoprene®** surface and a core of particularly tough and impact-resistant polypropylene. The special surface structure allows transmission of high torques, even with wet or oily hands. **Blade** of chrome vanadium special alloy combining maximum hardness and exceptional toughness.

Surface nickel-plated and chrome-plated, with black plane parallel stepped tip.

From size 8 with hexagon flats for wrench assistance.

Advantage:

- **Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.**
- **No cam-out effect.**
- **Tips perfectly fit standard and non-standard screw slot sizes.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

Application:

For repair and assembly work, for loosening tight screws etc.

Content:

1 each screwdriver No. 660030: Size 3.5; 4; 5.5; 6.5; 8

Technical description

Number of screwdrivers	5
Drive profile	Slot-head screwdriver
non-sparking	no
Type of product	Screwdrivers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/660031-5>