



Screwdriver for slot-head, with 2-component SwissGrip handle, Blade width b: 4mm



Order data

Order number	660040 4
GTIN	7610733244461
Item class	63E

Description

Version:

SwissGrip power grip with non-allergenic elastomer coating and a core of particularly tough and impact-resistant polypropylene. High torques can be exerted even with wet and oily hands. **Blade** of PB Swiss Tools special alloy combines maximum hardness with exceptional toughness. Surface nickel-plated and chrome-plated. Black tip. Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission. Handle with "Rainbow" colour coding for finding the correct drive size quickly.

Advantage:

- **Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.**
- **No cam-out effect.**
- **Tips perfectly fit standard and non-standard screw slot sizes.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

Application:

For repair and assembly work, for loosening tight screws etc.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.
Recommended product number: 660032

Technical description

Blade length	100 mm
Tip thickness a	0.6 mm
Blade width b	4 mm
overall length	195 mm
Actuation hexagon	no
through blade	no
Blade designation	2
Blade tip	black
Series	SwissGrip
Drive profile	Slot-head screwdriver
Type of shank	round
Impact cap	no
Material	PB Swiss Tools special alloy
Material of handle	Elastomer
Surface	nickel-plated and chrome-plated
Type of product	Screwdrivers