



Carbide-tipped hammer drill SDS-plus, Ø×overall length: 8X260mm



Order data

Order number	789000 8X260
GTIN	4002395320141
Item class	76G

Description

Version:

The 3 special Power Breaker projecting teeth of the M2 generate micro-cracks in the material being drilled, these promote quicker advance by the drill and faster removal of material. The high quality carbide tip with particularly strong brazed joint guarantees long tool life, even in reinforced concrete. The reinforced core flutes (KVS) are vibration-damping, so the impact energy is transmitted directly to the drilling tip.

Application:

For drilling concrete, natural stone, and masonry.

Note:

When using extra long drills (> 500 mm), first drill a pilot hole with a shorter drill of the same diameter (prevents bending and breakage).

Technical description

Number of cutting edges Z	2
Flute length	200 mm
overall length	260 mm
Ø	8 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

