



Carbide-tipped hammer drill set, Drill Ø: 5-12mm



Order data

Order number	789020 5-12
GTIN	4002395369980
Item class	76G

Description

Version:

- **2 cutting edges.** The 3 special Power Breaker projecting teeth of the MS2 generate micro-cracks in the material being drilled, these promote quicker advance by the drill and faster removal of material. The high quality carbide tip with particularly strong brazed joint guarantees long tool life, even in reinforced concrete. The reinforced core flutes (KVS) are vibration-damping, so the impact energy is transmitted directly to the drilling tip.

Application:

For drilling concrete, natural stone, and masonry.

Content:

Hammer drill No. 789000: 1 pc. each
size 5; 6; 8, length 110 mm;
size 6; 8; 10; 12 length 160 mm

Technical description

Drill Ø	5 - 12 mm
Number of cutting edges Z	2

Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

Accessories

Carbide-tipped hammer drill SDS-plus Ø×overall length 12X160 mm	789000 12X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X160 mm	789000 8X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 5X110 mm	789000 5X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 10X160 mm	789000 10X160
Carbide-tipped hammer drill SDS-plus Ø×overall length 8X110 mm	789000 8X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 6X110 mm	789000 6X110
Carbide-tipped hammer drill SDS-plus Ø×overall length 6X160 mm	789000 6X160