



Heavy-duty side cutter, polished, with return spring, overall length: 180mm



Order data

Order number	725230 180
GTIN	4003773060192
Item class	73F

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. **With return spring that can be engaged / disengaged.**

Pliers chemically blacked, head bright polished, handles with multi-component covering. High cutting performance due to optimum leverage.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Cutting capacity soft wire up to \varnothing : 3.8 mm

Cutting capacity hard wire up to \varnothing : 2.7 mm

Cutting capacity piano wire up to \varnothing : 2.2 mm

Technical description

Cutting capacity soft wire up to \varnothing	3.8 mm
Cutting capacity piano wire up to \varnothing	2.2 mm
overall length	180 mm
Cutting capacity hard wire up to \varnothing	2.7 mm
Standard	DIN ISO 5749
Handle	Thick-walled grip
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Material	Chromium vanadium steel
Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no
with selectable return spring	yes
Type of product	Cutting pliers