



Heavy-duty side cutter, polished, with return spring, overall length: 180mm



Order data

Order number	725230 180
GTIN	4003773060192
Item class	73F

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. **With return spring that can be engaged / disengaged.**

Pliers chemically blacked, head bright polished, handles with multi-component covering. High cutting performance due to optimum leverage.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	3.8 mm
Cutting capacity piano wire up to Ø	2.2 mm
overall length	180 mm
Cutting capacity hard wire up to Ø	2.7 mm
Standard	DIN ISO 5749
Handle	Thick-walled grip
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel

Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no
with selectable return spring	yes
Type of product	Cutting pliers