


**Side cutter ERGO™, chrome-plated, overall length: 125mm**

**Order data**

Order number	725240 125
GTIN	7314150106547
Item class	730

**Description**
**Version:**

Jaws chrome-plated. **Progressively ground cutting edges** additionally induction hardened (approx. 62 HRC). With strong chamfered cutting edges near to the joint for hard material and a finer chamfer on the tips for optimum cutting of soft material. Heavy-duty grips with **opening spring that can be engaged / disengaged**.

**Standard:**

**DIN ISO 5749**

**Material:**

Chrome vanadium steel, drop-forged and oil-hardened.

**Technical description**

Cutting capacity piano wire up to Ø	1.6 mm
overall length	125 mm
Standard	DIN ISO 5749
Handle	Heavy-duty ERGO® grip
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no

with selectable return spring

yes

Type of product

Cutting pliers