



## Side cutter, chrome-plated VDE insulated, overall length: 125mm



### Order data

Order number	725300 125
GTIN	4003773018124
Item class	73F

### Description

#### Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws chrome-plated, handles with multi-component covering.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

#### Standard:

**DIN ISO 5749**

#### Material:

Special tool steel, drop-forged, and oil-hardened.

### Technical description

Cutting capacity soft wire up to Ø	3 mm
overall length	125 mm
Cutting capacity hard wire up to Ø	1.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Special tool steel
Surface	chrome-plated

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers