



Carbide-tipped hammer drill "MX4" SDS-plus, Øxoverall length: 15X260mm



Order data

Order number	789050 15X260
GTIN	4002395376100
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. Sharper angled tip: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. 4-edged, slotted, robust and **one-part soldered-on** carbide insert. New head design in combination with acute-angle tip permits optimum feed when encountering rebar.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. 4-flute design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

Flute length	200 mm
overall length	260 mm
Number of cutting edges Z	4
Ø	15 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

