


Side cutter ERGO™, chrome-plated, overall length: 160mm

Order data

Order number	725240 160
GTIN	7314150106561
Item class	730

Description
Version:

Jaws chrome-plated. **Progressively ground cutting edges** additionally induction hardened (approx. 62 HRC). With strong chamfered cutting edges near to the joint for hard material and a finer chamfer on the tips for optimum cutting of soft material. Heavy-duty grips with **opening spring that can be engaged / disengaged**.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	2 mm
overall length	160 mm
Standard	DIN ISO 5749
Handle	Heavy-duty ERGO® grip
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no

with selectable return spring	yes
Type of product	Cutting pliers