



Diagonal side cutter chrome-plated, with grips, overall length: 180mm



Order data

Order number	724860 180
GTIN	4003773043706
Item class	73F

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).
Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity hard wire up to Ø	2.5 mm
Cutting capacity soft wire up to Ø	4 mm
overall length	180 mm
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chrome vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no

Type of product

Cutting pliers