



Carbide-tipped hammer drill set "MX4", Drill Ø: 5-10mm



Order data

| | |
|--------------|---------------|
| Order number | 789060 5-10 |
| GTIN | 4002395374915 |
| Item class | 76G |

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. TARGET TIP TECHNOLOGY - tip angled more acutely:

more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. Plastic case

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **4-flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Content:

Hammer drill No. 789050: 1 pc. each
size 5; 6 length 110 mm;
size 6; 8; 10 length 160 mm

Technical description

| | |
|----------------------------------|-----------------|
| Number of cutting edges Z | 4 |
| Drill Ø | 5 - 10 mm |
| Packaging | plastic box |
| Tool material | Carbide |
| Use with impact / without impact | Impact drilling |
| Shank | SDS Plus |
| Type of product | Masonry drill |

Accessories

| | |
|---|---------------|
| Carbide-tipped hammer drill "MX4" SDS-plus Ø×overall length 8X160 mm | 789050 8X160 |
| Carbide-tipped hammer drill "MX4" SDS-plus Ø×overall length 5X110 mm | 789050 5X110 |
| Carbide-tipped hammer drill "MX4" SDS-plus Ø×overall length 6X110 mm | 789050 6X110 |
| Carbide-tipped hammer drill "MX4" SDS-plus Ø×overall length 10X160 mm | 789050 10X160 |
| Carbide-tipped hammer drill "MX4" SDS-plus Ø×overall length 6X160 mm | 789050 6X160 |