



## Carbide-tipped hammer drill set "MX4", Drill Ø: 5-12 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 789060 5-12   |
| GTIN         | 4002395162147 |
| Item class   | 76G           |

### Description

#### Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. In a plastic case.

#### Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **4-flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

#### Content:

Hammer drill No. 789050: 1 pc. each  
size 5; 6; 8 length 110 mm;  
size 6; 8; 10; 12 length 160 mm  
Shank: SDS Plus  
Packaging: Plastic case

### Technical description

|           |              |
|-----------|--------------|
| Drill Ø   | 5 - 12 mm    |
| Packaging | Plastic case |

|                                  |                 |
|----------------------------------|-----------------|
| Number of cutting edges Z        | 4               |
| Tool material                    | Carbide         |
| Use with impact / without impact | Impact drilling |
| Shank                            | SDS Plus        |
| Type of product                  | Masonry drill   |

## Accessories

|   |               |
|---|---------------|
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 6X110 mm  | 789050 6X110  |
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 6X160 mm  | 789050 6X160  |
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 5X110 mm  | 789050 5X110  |
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 12X160 mm | 789050 12X160 |
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 8X160 mm  | 789050 8X160  |
| Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 10X160 mm | 789050 10X160 |