



Side cutter, chrome-plated VDE insulated, overall length: 160mm



Order data

Order number	725300 160
GTIN	4003773021995
Item class	73F

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws chrome-plated, handles with multi-component covering.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	4 mm
Cutting capacity hard wire up to Ø	2 mm
overall length	160 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Special tool steel
Surface	chrome-plated

Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers