



Carbide-tipped hammer drill "MX4" SDS-plus, Øxoverall length: 8X160mm



Order data

Order number	789050 8X160
GTIN	4002395366798
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. Sharper angled tip: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. 4-edged, welded-on carbide head.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. 4-flute design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

Flute length	100 mm
Number of cutting edges Z	4
overall length	160 mm
Ø	8 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

