



Diagonal side cutter, chrome-plated VDE insulated, overall length: 180 mm



Order data

Order number	725300 180
GTIN	4003773033813
Item class	73F

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC). **Plastic-coated handles to DIN EN 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Cutting capacity soft wire up to \varnothing : 4 mm

Cutting capacity hard wire up to \varnothing : 2.5 mm

Technical description

Cutting capacity hard wire up to \varnothing	2.5 mm
overall length	180 mm
Cutting capacity soft wire up to \varnothing	4 mm
Standard	DIN EN 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Special tool steel

Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers