

Garant
Precision diagonal side cutter, standard jaws, SFW, overall length: 130 mm


Order data

Order number	725390 130
GTIN	4045197166371
Item class	71B

Description

Version:

Slim head, cutting edges induction hardened and precision ground, fine chamfered.
Handles with plastic grips and opening spring.

Material:

Chrome vanadium steel, drop-forged and oil-hardened.
Cutting chamfer: very fine bevel
Cutting capacity soft wire up to \varnothing : 0.4 - 1.5 mm
Cutting capacity medium hard wire up to \varnothing : 0.4 - 1 mm

Technical description

Cutting capacity medium hard wire up to \varnothing	0.4 - 1 mm
overall length	130 mm
Cutting capacity soft wire up to \varnothing	0.4 - 1.5 mm
Cutting chamfer	very fine bevel
Handle	Plastic handle coverings
Manufacturing process	Cutting edges induction hardened and precision ground.
Material	Chrome vanadium steel, drop-forged and oil-hardened
Product name attribute	SFW

Arm with opening spring	yes
Type of product	Cutting pliers

Accessories

Spring set pack of 2	719270
----------------------	--------