



Carbide-tipped hammer drill "MX4" SDS-plus, Øxoverall length: 8X210mm



Order data

Order number	789050 8X210
GTIN	4002395366804
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. Sharper angled tip: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. 4-edged, welded-on carbide head.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. 4-flute design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

Number of cutting edges Z	4
Flute length	150 mm
overall length	210 mm
Ø	8 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

