

Garant**Side cutter, chrome-plated VDE insulated, overall length: 140mm**

Order data

| | |
|--------------|---------------|
| Order number | 725310 140 |
| GTIN | 4045197501639 |
| Item class | 71B |

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

| | |
|------------------------------------|---|
| Cutting capacity hard wire up to Ø | 1.8 mm |
| Cutting capacity soft wire up to Ø | 4 mm |
| overall length | 140 mm |
| Standard | DIN EN IEC 60900 / VDE 0682-201 |
| Standard | DIN ISO 5749 |
| Handle | Multi-component covering |
| Manufacturing process | Cutting edges induction hardened (approx. 62 HRC) |
| Material | Special tool steel |

| | |
|---------------------------------|----------------|
| Surface | chrome-plated |
| Heavy-duty diagonal side cutter | no |
| with selectable return spring | no |
| Type of product | Cutting pliers |