



Carbide-tipped hammer drill "MX4" SDS-plus, Øxoverall length: 20X250mm



Order data

Order number	789050 20X250
GTIN	4002395320974
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. Sharper angled tip: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. 4-edged, slotted, robust and **one-part soldered-on** carbide insert. New head design in combination with acute-angle tip permits optimum feed when encountering rebar.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. 4-flute design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Technical description

Ø	20 mm
Number of cutting edges Z	4
overall length	250 mm
Flute length	200 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

