



Side cutter polished, overall length: 180mm



Order data

Order number	724900 180
GTIN	4003773218074
Item class	73F

Description

Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).
Jaws chemically blacked, polished head, plastic coated handles.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity hard wire up to \emptyset	2.5 mm
Cutting capacity soft wire up to \emptyset	4 mm
overall length	180 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chemically blackened, head bright polished
Heavy-duty diagonal side cutter	no

with selectable return spring

no

Type of product

Cutting pliers