




Electronics side cutter, oval head, FW, overall length: 140mm



Order data

Order number	726000 140
GTIN	7314150103133
Item class	73M

Description

Version:

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters. **Suitable for ESDs**, with ergonomic **2-component** grips.

The patented opening spring reduces the resistance when closing the cutter. Thus the force is concentrated on the cut.

Material:

High-performance ball-bearing steel, drop forged, burnished.

Technical description

Cutting capacity copper wire up to Ø	0.3 - 1.6 mm
Head width	13 mm
overall length	140 mm
Cutter length	12.5 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	fine bevel
Material	High-performance ball-bearing steel
Head shape	oval
Handle	2-component grip

Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Surface	black burnished
Product name attribute	FW
with return spring	yes
adjustable precision screw joint	yes
Type of product	Cutting pliers