



Electrician's screwdriver for slot-head, with Kraftform handle fully insulated, Blade width b: 2,5mm



Order data

Order number	663100 2,5
GTIN	4013288027221
Item class	63H

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**.

Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Blades with taper tips, manufactured to the standard dimensions of slots on the screws. Fully insulated, the breakdown strength of the insulation is many times the minimum test voltage set by VDE. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Kraftform handle made of impact resistant plastic **with integral soft zones** facilitates torque transmission and thus protects hand and arm.

Blade of high-alloy special steel. Nicromatt chrome-plated surface, black tips or chemically nickel-coated Lasertip tips. From size 5.5 the outside \varnothing of the insulation is the same as the tip width (helpful when working in narrow spaces).

Application:

For use at voltage up to 1000 V.

Optimum working life for electrician's screwdrivers is assured if screwdrivers always exactly match the standard screw slot size. (see tables part). Incorrect screwdriver size selection will cause damage to the screw head.

Technical description

Tip thickness a	0.4 mm
Blade width b	2.5 mm
overall length	161 mm

Blade length	80 mm
Blade tip	black
Manufacturer's designation	160 i VDE
Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Slot-head screwdriver
Type of product	Screwdrivers