



## CoBolt® compact bolt cutter, overall length: 200 mm



### Order data

Order number	731750 200
GTIN	4003773033165
Item class	73F

### Description

#### Version:

Special compound action allows excellent cutting performance with relatively low applied force. Cutting edges induction hardened (approx. 64 HRC). Bolt cutter chemically blackened, plastic coated handles.

#### Application:

For wires up to 2000 N/mm<sup>2</sup> tensile strength.

#### Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.  
 for soft steel wire up to Ø: 6 mm  
 for medium-hard steel wire up to Ø: 5.2 mm  
 for piano wire up to Ø: 3.6 mm

### Technical description

overall length	200 mm
for piano wire up to Ø	3.6 mm
for medium-hard steel wire up to Ø	5.2 mm
for soft steel wire up to Ø	6 mm
Manufacturer's designation	CoBolt®
Blade	hardened
Handle	plastic coated
Material	Chrome vanadium electro-steel
Surface	chemically blacked

with return spring	no
Type of product	Cutting pliers