



CoBolt® compact bolt cutter with 20° angled head, overall length: 200mm



Order data

Order number	731755 200
GTIN	4003773066866
Item class	73F

Description

Version:

Special compound action allows excellent cutting performance with relatively low applied force. Cutting edges induction hardened (approx. 64 HRC).

Bolt cutter chemically blackened, plastic coated handles. **Head 20° offset for flush cutting.**

Application:

For wires up to 2000 N/mm² tensile strength.

Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.

Technical description

for soft steel wire up to Ø	6 mm
for medium-hard steel wire up to Ø	5.2 mm
for piano wire up to Ø	3.6 mm
overall length	200 mm
Manufacturer's designation	CoBolt®
Blade	hardened
angled head	20 degrees
Handle	plastic coated
Material	Chrome vanadium electro-steel
Surface	chemically blacked

with return spring	no
Type of product	Cutting pliers