



## Cable cutter with 2-component grips VDE insulated, overall length: 165mm



### Order data

Order number	730350 165
GTIN	4003773039648
Item class	73F

### Description

#### Version:

Handles with **insulation up to 1000 volts to DIN EN IEC 60900 / VDE 0682-201**.

Handles with multi-component coverings. Head with sickle-shaped blades. Handles with plastic grips. Cuts smoothly and cleanly without crushing.

#### Application:

For cutting copper and aluminium cables.

#### Material:

**Special tool steel**, drop-forged.

### Technical description

overall length	165 mm
Cutting capacity	50 mm <sup>2</sup>
Cutting capacity up to Ø	15 mm
Protection against trapping fingers	yes
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Operation	mechanical, single-handed
Material	Special quality tool steel, drop-forged, oil-hardened
Surface	chrome-plated

with return spring	no
Type of product	Scissors