



Carbide-tipped hammer drill, SDS-max, Ø×overall length: 40X570mm



Order data

| | |
|--------------|---------------|
| Order number | 789200 40X570 |
| GTIN | 4002395374533 |
| Item class | 76G |

Description

Version:

Special carbide insert geometry for longer tool lives.

Tip angled more acutely: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed. PGM-certified – approves precise drilled holes suitable for plugs, both for chemical and mechanical anchors. Large flute channels for quick evacuation of waste material, resulting in less friction.

Drill head with square cross section from Ø 16 mm.

Application:

For drilling concrete, natural stone, and masonry.

Note:

When using long drills > 500 mm, first drill a pilot hole at least 150 mm deep with a shorter drill (preferably of the same Ø).

Technical description

| | |
|----------------------------------|-----------------|
| Ø | 40 mm |
| Number of cutting edges Z | 2 |
| overall length | 570 mm |
| Flute length | 450 mm |
| Tool material | Carbide |
| Use with impact / without impact | Impact drilling |
| Shank | SDS Max |
| Type of product | Masonry drill |

