

**Wire rope cutter, overall length: 190mm****Order data**

Order number	731550 190
GTIN	4003773040651
Item class	73F

Description**Version:**

Sturdy design, drop-forged from solid steel. With screw joint and opening spring. Cutter edge hardness 64 HRC. Handles with light PVC coating.

With integral opening spring and locking lever. Two integral compression profiles for Bowden cable end caps and wire rope end bushes.

Application:

For cutting wire ropes, multi-core cables etc.

Material:

Chrome vanadium special steel, oil-hardened.

Technical description

overall length	190 mm
for round steel bar (maximum 1200 N/mm ²) Ø	4 mm
for piano wire Ø	2.5 mm
for wire ropes (maximum 1600 N/mm ²) Ø	5 mm
Type of product	Cutting pliers