



Cable cutter with 2-component grips VDE insulated, overall length: 200mm



Order data

Order number	730350 200
GTIN	4003773026761
Item class	73F

Description

Version:

Handles with **insulation up to 1000 volts to DIN EN IEC 60900 / VDE 0682-201**.

Handles with multi-component coverings. Head with sickle-shaped blades. Handles with plastic grips. Cuts smoothly and cleanly without crushing.

Double blade gives particularly high cutting range.

Application:

For cutting copper and aluminium cables.

Material:

Special tool steel, drop-forged.

Technical description

Cutting capacity up to Ø	20 mm
overall length	200 mm
Cutting capacity	70 mm ²
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Operation	mechanical, single-handed
Material	Special quality tool steel, drop-forged, oil-hardened
Surface	chrome-plated

with return spring	no
Type of product	Scissors