

**Cable cutter with compound action VDE insulated, for cable Ø: 32mm****Order data**

Order number	731150 32
GTIN	4003773026884
Item class	73F

**Description****Version:**

Cutter head with sickle shaped blade and compound action (one handed operation). Double blades ensure square cut.

**Insulation up to 1000 Volts to DIN EN 60900 / VDE 0682-201.**

**Application:**

For clean cutting of aluminium and copper cables (even flex cables). Not for use on steel wire, hard aluminium alloys, hard drawn copper conductors.

**Material:**

Special steel blade, coated sheet metal handles.

**Note:**

On single-core cables the cutting force is around 30 % less.

Cutting capacity multi-core cable up to: 240 mm<sup>2</sup>

overall length: 250 mm

**Technical description**

for cable Ø	32 mm
overall length	250 mm
Cutting capacity multi-core cable up to	240 mm <sup>2</sup>
Protection against trapping fingers	yes
Standard	DIN EN 60900 / VDE 0682-201

Handle	Multi-component covering
Operation	mechanical, single-handed, ratchet principle
Material	Special quality tool steel, drop-forged, oil-hardened
Type of product	Scissors

---

## Accessories

Moving blade including nut and bolt Suitable for cable Ø 32 mm	731130 32
--	-----------