



Cable cutter with compound action VDE insulated, for cable Ø: 52mm



Order data

Order number	731150 52
GTIN	4003773026891
Item class	73F

Description

Version:

Cutter head with sickle shaped blade and compound action (one handed operation). Double blades ensure square cut.

Insulation up to 1000 Volts to DIN EN 60900 / VDE 0682-201.

Application:

For clean cutting of aluminium and copper cables (even flex cables). Not for use on steel wire, hard aluminium alloys, hard drawn copper conductors.

Material:

Special steel blade, coated sheet metal handles.

Note:

On single-core cables the cutting force is around 30 % less.

Cutting capacity multi-core cable up to: 380 mm²

overall length: 280 mm

Technical description

for cable Ø	52 mm
overall length	280 mm
Cutting capacity multi-core cable up to	380 mm ²
Protection against trapping fingers	yes
Standard	DIN EN 60900 / VDE 0682-201

Handle	Multi-component covering
Operation	mechanical, single-handed, ratchet principle
Material	Special quality tool steel, drop-forged, oil-hardened
Type of product	Scissors

Accessories

Moving blade including nut and bolt Suitable for cable Ø 52 mm	731130 52
--	-----------