

LINDSTRÖM

**Electronics side cutter, oval head, kW, overall length: 110mm****Order data**

Order number	726280 110
GTIN	7314150051007
Item class	73M

**Description****Version:**

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs**. Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

**Material:**

High performance steel alloy, drop forged, burnished.

**Technical description**

Cutting capacity copper wire up to Ø	0.1 - 1 mm
overall length	110 mm
Head width	10 mm
Cutter length	10 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	High-performance steel alloy
Head shape	oval
Handle	Plastic covering

Manufacturing process	induction hardened cutting edges (63 – 65 HRC)
Surface	black burnished
Product name attribute	kW
with return spring	yes
Type of product	Cutting pliers