


CoBolt® compact bolt cutter with grips, overall length: 200mm

Order data

Order number	731740 200
GTIN	4003773047056
Item class	73F

Description
Version:

Special compound action allows excellent cutting performance with relatively low applied force. Cutting edges induction hardened (approx. 64 HRC).

Jaws chemically blackened, handles with multi-component covering.

Application:

For wires up to 2000 N/mm² tensile strength.

Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.

Technical description

for soft steel wire up to Ø	6 mm
for medium-hard steel wire up to Ø	5.2 mm
for piano wire up to Ø	3.6 mm
overall length	200 mm
Manufacturer's designation	CoBolt®
Blade	hardened
Handle	Multi-component covering
Material	Chrome vanadium electro-steel
Surface	chemically blacked
with return spring	no

Type of product

Cutting pliers