

LINDSTRÖM

Electronics side cutter, oval head, kW, overall length: 113mm**Order data**

| | |
|--------------|---------------|
| Order number | 726280 113 |
| GTIN | 7314150052097 |
| Item class | 73M |

Description**Version:**

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs.** Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Technical description

| | |
|--------------------------------------|------------------------------|
| overall length | 113 mm |
| Head width | 12.5 mm |
| Cutting capacity copper wire up to Ø | 0.2 - 1.25 mm |
| Cutter length | 12.5 mm |
| electrostatic characteristic | EGB/ESD |
| Cutting chamfer | without bevel |
| Material | High-performance steel alloy |
| Head shape | oval |
| Handle | Plastic covering |

| | |
|------------------------|--|
| Manufacturing process | induction hardened cutting edges (63 – 65 HRC) |
| Surface | black burnished |
| Product name attribute | kW |
| with return spring | yes |
| Type of product | Cutting pliers |