



## CoBolt® compact bolt cutter with grips and opening spring, overall length: 200mm



### Order data

Order number	731745 200
GTIN	4003773066859
Item class	73F

### Description

#### Version:

Special compound action allows excellent cutting performance with relatively low applied force. Cutting edges induction hardened (approx. 64 HRC).

Jaws chemically blackened, handles with multi-component covering. **With opening spring** and integral lock.

#### Application:

For wires up to 2000 N/mm<sup>2</sup> tensile strength.

#### Material:

Chrome vanadium electro-steel, drop-forged and oil-hardened.

for soft steel wire up to Ø: 6 mm

for medium-hard steel wire up to Ø: 5.2 mm

for piano wire up to Ø: 3.6 mm

### Technical description

for soft steel wire up to Ø	6 mm
for medium-hard steel wire up to Ø	5.2 mm
for piano wire up to Ø	3.6 mm
overall length	200 mm
Manufacturer's designation	CoBolt®
Blade	hardened
Handle	Multi-component covering

Material	Chrome vanadium electro-steel
Surface	chemically blacked
with return spring	yes
Type of product	Cutting pliers