

► LINDSTRÖM

Electronics side cutter, pointed head, hollowed jaws, kW, overall length: 110mm



Order data

Order number	726420 110
GTIN	7314150051090
Item class	73M

Description

Version:

Slim shape with precision ground induction hardened cutting edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips made of conductive material with opening spring.

Suitable for ESDs. Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Technical description

Cutting capacity copper wire up to Ø	0.1 - 0.8 mm
Head width	10 mm
overall length	110 mm
Cutter length	10 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	High-performance steel alloy
Head shape	pointed, hollowed
Handle	Plastic covering

Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Surface	black burnished
Product name attribute	kW
with return spring	yes
Type of product	Cutting pliers