

▶ LINDSTRÖM

Electronics oblique end cutter, SFW, overall length: 108mm**Order data**

Order number	726912 108
GTIN	7314150052554
Item class	73M

Description**Version:**

With precision ground inductive hardened cutting edges (63–65 HRC). White plastic grips of conductive material with return spring. **Suitable for ESDs.** Specially made box joint with particularly long contact faces, undesired movements in the joint are minimised, which ensures extremely precise axial alignment of the jaws.

Material:

Special ball bearing steel, drop-forged.

Technical description

Head width	10.5 mm
Cutting capacity copper wire up to Ø	0.35 - 1.25 mm
overall length	108 mm
Cutter length	15 mm
Head length	8 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	very fine bevel
Handle	Plastic covering

Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Material	Special ball-bearing steel
Product name attribute	SFW
with return spring	yes
Type of product	Cutting pliers