

LINDSTRÖM

Electronics side cutter, oval head, FW, overall length: 113mm**Order data**

Order number	726240 113
GTIN	7314150051113
Item class	73M

Description**Version:**

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs.** Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

Material:

High performance steel alloy, drop forged, burnished.

Technical description

Cutting capacity copper wire up to Ø	0.3 - 1.6 mm
overall length	113 mm
Head width	12.5 mm
Cutter length	12.5 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	fine bevel
Material	High-performance steel alloy
Head shape	oval
Handle	Plastic covering

Manufacturing process	induction hardened cutting edges (63 – 65 HRC)
Surface	black burnished
Product name attribute	FW
with return spring	yes
Type of product	Cutting pliers