



## Electronics side cutter, pointed head with wire holder, W, overall length: 125Hmm



### Order data

Order number	726460 125H
GTIN	4003773240518
Item class	73F

### Description

#### Version:

Pointed shape with strong cutting chamfer, especially for hard wires. Adjustable screw joint. Jaws burnished, handles with plastic coating.

#### Standard:

**DIN ISO 9654**

#### Material:

Special tool steel, drop-forged, and oil-hardened.

### Technical description

overall length	125 mm
Head width	10.5 mm
Cutter length	14 mm
Cutting capacity medium-hard steel wire	0.2 - 1 mm
Cutting capacity hard steel wire	0.2 - 0.6 mm
Cutting chamfer	large bevel
Material	Special tool steel
Head shape	pointed

Standard	DIN ISO 9654
Handle	Plastic covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Surface	burnished
Product name attribute	W
with return spring	yes
with wire holder	yes
Type of product	Cutting pliers