



Electronics side cutter Super Knips[®], kW, overall length: 125mm



Order data

Order number	726480 125
GTIN	4003773035381
Item class	73F

Description

Version:

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

Standard:

DIN ISO 9654

Material:

Made of stainless steel (INOX).

Technical description

overall length	125 mm
Head width	13.5 mm
Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
Cutter length	9 mm
Cutting capacity medium-hard steel wire	0.2 - 1 mm
Cutting chamfer	without bevel
Material	Stainless steel, INOX
Standard	DIN ISO 9654
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 54 HRC)
Product name attribute	kW
with return spring	yes
with wire holder	no
Type of product	Cutting pliers