

Electronics side cutter clean cut, stronger jaws, kW, overall length: 130 mm



Order data

Order number	726700 130
GTIN	4250157116406
Item class	76B

Description

Version:

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use.

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Cutting chamfer: without bevel

Material: Carbon steel (C70)

Head width: 13.5 mm

Cutter length: 8 mm

Cutting capacity copper wire up to Ø: 1.3 mm

Technical description

Cutting capacity copper wire up to Ø	1.3 mm
Head width	13.5 mm
overall length	130 mm
Cutter length	8 mm
Cutting chamfer	without bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	kW

with return spring

yes