

LINDSTRÖM

**Electronics side cutter, oval head, SFW, overall length: 110mm****Order data**

Order number	726260 110
GTIN	7314150050987
Item class	73M

**Description****Version:**

Slim style with precision ground induction hardened jaw edges (63 – 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs.** Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

**Material:**

High performance steel alloy, drop forged, burnished.

**Technical description**

overall length	110 mm
Cutting capacity copper wire up to Ø	0.1 - 1.25 mm
Head width	10 mm
Cutter length	10 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	very fine bevel
Material	High-performance steel alloy
Head shape	oval
Handle	Plastic covering

Manufacturing process	induction hardened cutting edges (63 – 65 HRC)
Surface	black burnished
Product name attribute	SFW
with return spring	yes
Type of product	Cutting pliers