


**Electronics side cutter Super Knips<sup>®</sup>, slender head, kW, overall length: 125mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 726610 125    |
| GTIN         | 4003773039778 |
| Item class   | 73F           |

**Description**
**Version:**

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

**Standard:**

**DIN ISO 9654**

**Material:**

Special tool steel, burnished.

**Technical description**

|  |                          |
|--|--------------------------|
| Head width                                       | 12.5 mm                  |
| overall length                                   | 125 mm                   |
| Cutting capacity copper wire up to $\varnothing$ | 0.2 - 1 mm               |
| Cutter length                                    | 9 mm                     |
| Cutting chamfer                                  | without bevel            |
| Material   | Special tool steel       |
| Head shape                                       | narrow                   |
| Standard   | DIN ISO 9654             |
| Handle   | Multi-component covering |

|                        |   |
|------------------------|---|
| Manufacturing process  | Cutting edges induction hardened (approx. 60 HRC) |
| Surface                | burnished   |
| Product name attribute | kW  |
| with return spring     | yes   |
| with wire holder       | no  |
| Type of product        | Cutting pliers                                    |